

2510FF4

FHP Manual Starter - Flush Mount - 2P - Key Operated - No Indicator - 277VAC



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 128.21 USD



Main

Product or component type	Single Unit Manual Starter
Range of product	F
Thermal overload type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	Without
Motor power hp	1 hp at 115 V AC 1 hp at 277 V AC 0.75 hp at 115 V DC 0.75 hp at 230 V DC 2 hp at 230 V AC
System Voltage	277 V AC 230 V DC
Poles description	2P
Control type	Key
Phase	1 phase
Local signalling	No indicator
Reset	Manual
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 12 (copper)
Height	4.5 in
Width	2.75 in
Depth	2.19 in

Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA degree of protection	Not rated (flush plate) sheet steel standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0.54000000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**