Product data sheet
Characteristics

2510FW2PH
FHP Manual Starter - NEMA 4 - 2 Conduit Opening - 2P - Red Indicator - 277VAC

Product availability: Non-Stock - Not normally stocked in distribution facility

Commercial status
This Product is Obsolete : JUN 30, 2020

⚠ This Product is Obsolete

Main

Product or Component Type	Single Unit Manual Starter
Range of Product	F
Thermal overload type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	0.75 NPT (top and bottom)
Maximum Horse Power Rating	1 Hp 115 V AC 1 Hp 277 V AC 0.75 Hp 115 V DC 0.75 Hp 230 V DC 2 Hp 230 V AC
[Ue] rated operational voltage	277 V AC 230 V DC
Poles description	2P
Control Type	Toggle switch (with lock-off)
Phase	1 phase
Local signalling	Red indicator
Reset	Manual
Motor starter type	Non reversing
Electrical Connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 12 copper
Height	4.38 In (111.25 mm)
Width	3 In (76.20 mm)
Depth	4.56 In (115.82 mm)

Environment

Product Certifications	UL listed file E42243 CCN NLRV[RETURN]CSA LR25490 class 3211 05
NEMA degree of protection	NEMA 4 die cast zinc alloy standard size

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	US10CP121101
Discount Schedule	0CP1
GTIN	00785901342304
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACh free of SVHC	Yes
EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
PVC free	Yes

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block