

# Product data sheet

## Characteristics

# 2510KG5A

Manual Switch - NEMA 1 - 2P - Toggle Operated - Red Indicator - 600VAC



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 156.57 USD



### Main

Product or component type	Single Unit Manual Switch
Range of product	K

### Complementary

Line Rated Current	30 A
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
Motor power hp	2 hp at 115 V AC 1 hp at 90 V DC 2 hp at 115 V DC 1.5 hp at 230 V DC 10 hp at 575 V AC 3 hp at 230 V AC 7.5 hp at 460 V AC
System Voltage	600 V AC 230 V DC
Poles description	2P
Control type	Toggle
Phase	1 phase
Local signalling	Red indicator 115 V
Motor starter type	Non reversing
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 10 (copper)
Height	4.25 in
Width	2.44 in
Depth	2.75 in


## Environment

Product certifications	CE UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA degree of protection	NEMA 1 plastic standard size

## Ordering and shipping details

Category	21102 - 2510,2511,2512 K
Discount Schedule	CP1
GTIN	00785901931256
Nbr. of units in pkg.	1
Package weight(Lbs)	0.88
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider- Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**