

# Product data sheet

## Characteristics

# 2510TBG2V06P11

## Manual Starter - NEMA 1 - Toggle - 3P - Size M0 - Red Indicator - 600VAC



Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 445.87 USD



### Main

Product or component type	Manual Starter
Range of product	T
NEMA size	M-0

### Complementary

Control type	Toggle switch
Local signalling	Red indicator, 480 V
Motor power hp	3 hp at 200...230 V AC 3 phases 5 hp at 380...575 V AC 3 phases
System Voltage	600 V AC
Poles description	3P
Motor starter type	Non reversing
Electrical connection	Pressure wire clamp
Thermal overload type	Melting alloy
Number of thermal units required	3
AWG gauge	AWG 14...AWG 8 (copper)
Auxiliary contact composition	Without
Height	8.63 in
Width	5 in
Depth	4.13 in

### Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA degree of protection	NEMA 1 painted sheet steel

### Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	4.8100000000000005
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	<b>Commercialised</b>
-----------------------	-----------------------