

Product data sheet

Characteristics

2512FG11P

Two Speed Manual Starter - NEMA 1 - 1P -
Toggle - Two Red Indicators - 277VAC



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 494.90 USD



Main

Product or component type	Duplex Unit Manual Starter
Range of product	F
Thermal overload type	Melting alloy

Complementary

Line Rated Current	16 A
Cable entry	0.5" and 0.75" knock-outs (top and bottom)
Motor power hp	1 hp at 115 V AC 1 hp at 230 V AC 1 hp at 277 V AC
System Voltage	277 V AC
Poles description	1P
Control type	Toggle switch
Phase	1 phase
Local signalling	Red indicator
Reset	Manual
Motor starter type	2 speed
Electrical connection	Screw clamp terminals
AWG gauge	AWG 14...AWG 12 (copper)
Height	4.25 in
Width	4.5 in
Depth	2.75 in

Environment

Product certifications	CE UL listed file E42243 CCN NLRV CSA LR25490 class 3211 05
NEMA degree of protection	NEMA 1 plastic standard size

Ordering and shipping details

Category	21101 - 2510,2511,2512 F
Discount Schedule	CP1
GTIN	00785901006268
Nbr. of units in pkg.	1
Package weight(Lbs)	1.8100000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------