

# Product data sheet

## Characteristics

# 2512MBO1

Two Speed Manual Starter - Open Device - Buttons - 3P - Size M0 - 600VAC



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 944.72 USD



### Main

Product or component type	Manual Starter
Range of product	M
NEMA size	M-0

### Complementary

Control type	Push-button
Local signalling	No indicator
Motor power hp	2 hp at 200...230 V AC 3 phases 3 hp at 380...575 V AC 3 phases
System Voltage	600 V AC
Poles description	3P
Motor starter type	2 speed
Electrical connection	Screw clamp terminals
Thermal overload type	Melting alloy
Number of thermal units required	3
AWG gauge	AWG 14...AWG 8 (copper)
Auxiliary contact composition	Without
Height	5.72 in
Width	3.5 in
Depth	4.03 in

### Environment

Product certifications	UL listed file E42243 CCN NLRV CSA LR60905 class 3211 05
NEMA degree of protection	Not rated (open device)

### Ordering and shipping details

Category	21103 - 2510,2511,2512 M,T
Discount Schedule	CP1
GTIN	00785901332688
Nbr. of units in pkg.	1
Package weight(Lbs)	8.9000000000000004
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**