

Product data sheet

Characteristics

29402

voltage release Compact MN - 12 V DC

Price*: 717.00 USD



Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Device short name	MN
Product or component type	Voltage release
Device application	Control
Range compatibility	Compact NS Compact NB Compact NR Compact NSF Compact NSJ
Voltage release type	Undervoltage release
[Uc] control circuit voltage	12 V DC

Complementary

Threshold tripping voltage	0.35...0.7 Un opening 0.85 Un closing
Supply holding power	< 5 W
Response time	< 50 ms
Auxiliary connection terminal	Screw terminal 0.00...0.00 in ² (0... 1.5 mm ²)

Ordering and shipping details

Category	01103-H,J,COMPACT NS UL/IEC CB ACCESS
Discount Schedule	DE2
GTIN	00785901110064
Package weight(Lbs)	0.26 Lb(US) (0.118 kg)
Returnability	No

Packing Units

Package 1 Height	0.630 Dm
Package 1 width	0.400 Dm
Package 1 Length	0.820 Dm

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : End of commercialisation