



Main

Range of product	NS100...250 INV100...250 INS250
Range	Compact
Device short name	CT module and voltage output
Product or component type	Current transformer
Device application	Control
Range compatibility	Compact INS circuit breaker Compact INV circuit breaker Compact NS circuit breaker
Poles description	4P
[In] rated current	100 A 125 A

Complementary

Current transformer ratio	125/5 A
---------------------------	---------

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
-------------------	--

Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**

29462 may be replaced by any of the following products:



LV429462

current transformer module with voltage measurement output, Compact NSX 100/160/250, 125 A rating, 4
Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2009 | Incompatible de montage ancienne/nouvelle gamme



LV429462

current transformer module with voltage measurement output, Compact NSX 100/160/250, 125 A rating, 4
Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2009 | Incompatible de montage ancienne/nouvelle gamme



LV429462

current transformer module with voltage measurement output, Compact NSX 100/160/250, 125 A rating, 4 poles
Qty 1

Reason for Substitution: End of life | Substitution date: 01 Jan 2009 |



LV429462

current transformer module with voltage measurement output, Compact NSX 100/160/250, 125 A rating, 4 poles
Qty 1

Reason for Substitution: Rebrand | Substitution date: 03 Jan 2019 |
