



Main

Range of product	Polinorma
Product or component type	Cable tray
Cable tray type	Unperforated
Colour	Grey (RAL 7030)
Quantity per set	12 m

Complementary

Material	PVC (polyvinyl chloride)
Height	40 mm
Width	150 mm
Length	3000 mm
Thickness	2.2 mm

Environment

Flame retardance	V0
Standards	IEC 61537 EN 60695-11-10 UNE 23727
Ambient air temperature for operation	-20...60 °C
IP degree of protection	IP44
IK degree of protection	IK10

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1833 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**