



### Main

Range of product	Polinorma
Product or component type	External riser
Provided equipment	Cover
Colour	Grey (RAL 7030)


### Complementary

Operating angle	90 °
Direction change type	Vertical
Inner radius	341 mm
Material	PVC (polyvinyl chloride)
Height	60 mm
Width	150 mm

### Environment

Flame retardance	V0
Standards	IEC 61537 EN 60695-11-10 UNE 23727
Ambient air temperature for operation	-20...60 °C
IK degree of protection	IK10

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0735 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
------------------------	--

Product Life Status : **Commercialised**