

Main

Range of product	Polinorma
Product or component type	Horizontal bracket
Colour	Grey (RAL 7030)
Quantity per set	Set of 4


Complementary

Permanent permissible load	240 kg
Product destination	Cable tray - 60 mm x 300 mm Cable tray - 100 mm x 300 mm
Mounting support	Wall
Material	PVC (polyvinyl chloride)
Height	133 mm
Width	80 mm
Depth	360 mm

Environment

Flame retardance	V0
Standards	IEC 61537 EN 60695-11-10 UNE 23727
Ambient air temperature for operation	-20...60 °C
IK degree of protection	IK10

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.