

Product data sheet

Characteristics

4X30T2FSS

TRANSFORMER DRY 3PH 30KVA

480V-208Y/120V



by Schneider Electric



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 42322.00 USD

Main

Product or component type	Dry Sealed Transformer
Number of tap-offs	2 5 % FCBN

Complementary

Box number	55X
Phase	3 phases
Primary voltage	480 V delta : 208Y/120 V
Rated power in VA	30 kVA
Temperature rise	115 °C
Height	31.5 in
Width	31.5 in
Depth	16.25 in
Enclosure mounting	Floor
Enclosure material	Stainless steel

Environment

NEMA degree of protection	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	CSA CULus UL listed

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
Nbr. of units in pkg.	1
Package weight(Lbs)	775
Returnability	N
Country of origin	US

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1430 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Phenyl glycidyl ether, which is known to the State of California to cause cancer and-birth defects or other reproductive harm.

----- Substance 2	Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**