

Commercial status

End of Commercialisation :

 End of Commercialisation

Main

Range	Thorsman
Product name	Thorsman POL
Product or component type	Pole
Type of pole	Two installation boxes
Device presentation	Empty
Provided equipment	2000 Mm flexible conduit
Colour tint	Natural
Quantity per set	Set of 1

Complementary

Pole/post surface finish	Anodized
Pole fixing mode	Free-standing
Front opening size	80 mm
Material	Aluminium anodized
Length	94 Mm
Height	2465 Mm
Width	205 Mm

Environment

Standards	PrEN 50085-2-4 SS 424 10 32 : 1989
Ambient air temperature for operation	-25...40 °C
IP degree of protection	IP30

Offer Sustainability

EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **End of commerc. - Block**

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.