



Main

Range of product	Thorsman
Product name	Thorsman CYB
Product or component type	Slave socket-outlet
Device presentation	Connection kit
Provided equipment	-
Colour tint	Black RAL 9005
Quantity per set	Set of 1

Complementary

Device composition	End piece
[In] rated current	16 A
[Ue] rated operational voltage	250 V
Number of power socket outlets	2 x 2P + E with shutters side earth
Ground lug position	37° ground lug
Device connection	Plug into master or slave outlet
Connections - terminals	Flat pads for crimped lug
Fixing mode	Snap-fitted
Material	PC/ABS
Length	94 mm
Height	84 mm
Width	39 mm

Environment

Standards	IEC 60884-1
Ambient air temperature for operation	-20...40 °C
IP degree of protection	IP20

Product Life Status : **Commercialised**