



Main

Range	ZENcelo
Product or component type	Switch
Device application	Bell switch
Load type	Resistive
Colour tint	Bronze

Complementary

Device mounting	Flush Surface
Number of gangs	1 gang
Connections - terminals	Clamp terminal
Width	70.1 Mm
Height	45.6 Mm
Depth	34.1 Mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
Product certifications	CCC
Standards	IEC 60669-1 GB 16915.1
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Product Life Status : **Commercialised**