



Main

Range	ZENcelo
Product or component type	Switch
Load type	Resistive Capacitive Inductive
Colour tint	Bronze


Complementary

Device mounting	Surface Flush
Switch function	2-way
Number of gangs	1 gang
Connections - terminals	Clamp terminal
Width	34.85 Mm
Height	45.8 Mm
Depth	32.8 Mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
Product certifications	CCC
Standards	IEC 60669-1 GB 16915.1
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Toxic heavy metal free	Yes
Mercury free	Yes

RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**