



Main

Range	ZENcelo
Product or component type	Telephone socket
Socket additional information	Shuttered
Colour tint	Bronze

Complementary

Device mounting	Flush Surface
Width	23.2 Mm
Height	46 Mm
Depth	30.4 Mm

Environment

Environmental characteristic	UV resistant
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %

Offer Sustainability

EU RoHS Directive	Not compliant
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Product Life Status : **Commercialised**

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.