



Main

Range	ZENcelo
Product or component type	TV/FM/SAT socket
TV socket type	TV
TV connector	Coaxial
Colour tint	Bronze

Complementary

Device mounting	Flush Surface
Material	Polycarbonate
Bandwidth	5...1000 Hz TV
Width	23.2 mm
Height	46 mm
Depth	24.3 mm

Environment

Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	0...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**