

Main

Range	ZENcelo
Product or component type	Switch
Load type	Capacitive Inductive Resistive
Colour tint	White

Complementary

Device mounting	Flush Surface
Switch function	2-way
Number of gangs	1 gang
Connections - terminals	Clamp terminal
Width	23.1 mm
Height	45.8 mm
Depth	32.8 mm

Environment

Ambient air temperature for operation	-5...45 °C
Ambient air temperature for storage	-5...60 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant
Operating altitude	2000 m
Product certifications	CCC
Standards	GB 16915.1 IEC 60669-1
IP degree of protection	IP20

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant Schneider Electric Declaration Of Conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Product Life Status : **Commercialised**