

Product data sheet

Characteristics

8536SCW13V08H30

Non-Reversing Starter Size 1, 3-Pole, Motor Logic SSOLR (Class 10/20), NEMA 4/4X



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Starter
Range of product	S
Control circuit	Common control circuit

Complementary

[Uc] control circuit voltage	208 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	27 A
Poles description	3P
Phase	3 phases
Rated power in HP	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control type	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	1
Height	13.19 in (335 mm)
Depth	7.8 in (198 mm)
Width	6.38 in (162 mm)


Environment

NEMA degree of protection	NEMA 4/4X brushed stainless steel
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21203 - 8502,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	13.620000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**