

8536SDO1V06H30S

Non-Reversing Starter Size 2, 3-Pole, Motor Logic
SSOLR, Open +Options



Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Product or component type	Starter
Range of product	S
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	440 V AC 50 Hz 480 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	45 A
Poles description	3P
Phase	3 phases
Rated power in HP	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control type	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	2
Height	7.8 in (198 mm)
Depth	4.92 in (125 mm)
Width	4.29 in (109 mm)


Environment

NEMA degree of protection	Not rated (open device)
Product certifications	CSA NEMA UL listed

Ordering and shipping details

Category	21192 - 8502,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901982951
Nbr. of units in pkg.	1
Package weight(Lbs)	7.75
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Product Life Status : **Commercialised**