

Product data sheet

Characteristics

8538SBA21V01CS

Non-Rever. Combo Starter Size 0, 3P, Melting Alloy Overload, NEMA 12 +Options



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1979.00 USD



Main

Product or component type	Combination Starter
Range of product	S
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	24 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Poles description	3P
Motor power hp	3 hp 230 V AC 3 phases 5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases 3 hp 200 V AC 3 phases
System Voltage	600 V AC
Control type	Selector switch (HAND-OFF-AUTO)
Auxiliary contact composition	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnecter device type	Non-fusible disconnect switch
NEMA size	0
Height	24 in
Depth	8.34 in
Width	9.5 in
Length	3.25 in

Environment

NEMA degree of protection	NEMA 12 painted sheet steel and with external reset
Product certifications	CSA UL listed

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
GTIN	00785901971375
Nbr. of units in pkg.	1
Package weight(Lbs)	46
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**