

Product data sheet

Characteristics

8538SBG13V02H308S

Non-Rever. Combo Starter Size 0, 3P, Motor Logic SSOLR, NEMA 1 +Options



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1437.00 USD



Main

Product or component type	Combination Starter
Range of product	S
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Line Rated Current	18 A
Poles description	3P
Motor power hp	5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases
System Voltage	600 V AC
Control type	No control units
Auxiliary contact composition	Without
Thermal overload type	Solid state Motor Logic class 10/20 1.5...4.5 A FLA
Disconnecter device type	Fusible disconnect switch, Type H and K Fuse, 30 A
NEMA size	0
Height	22.5 in
Depth	8.34 in
Width	9.5 in
Length	3.25 in


Environment

NEMA degree of protection	NEMA 1 painted sheet steel and with external reset
Product certifications	CSA UL listed

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	35
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1545 - Schneider Electric declaration of conformity  Schneider-Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------