

Product data sheet

Characteristics

8539SBA41V06C

COMBO STARTER 600VAC 18A NEMA



by Schneider Electric

Price*: 2492.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Contact application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure dust and damp proof indoor

Complementary

System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Control type	Selector switch HAND-OFF-AUTO
Depth	8.34 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	24 in
Motor power hp	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
NEMA size	0
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker GJL36003M01
Product weight	40 lb(US)
Reset	Without external
Short-circuit protection	100000 A AIR
Thermal overload type	Melting alloy
Width	9.5 in

Environment

NEMA degree of protection	NEMA 12
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21212 - 8538,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months

Product Life Status : **End of commercialisation**