

# Product data sheet

## Characteristics

# 8539SBW41V06

## COMBO STARTER 600VAC 18A NEMA



by Schneider Electric

Price\*: 3182.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Contact application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnect device type	Mag-Gard circuit breaker
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure corrosion resistance indoor/outdoor

### Complementary

System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Depth	8.34 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	24.06 in
Motor power hp	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
NEMA size	0
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker GJL36003M01
Product weight	40 lb(US)
Short-circuit protection	100000 A AIR
Thermal overload type	Melting alloy
Width	9.5 in

### Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E152395 CCN NKJH7

### Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	40
Returnability	N

### Offer Sustainability

RoHS (date code: YYWW)

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period

18 months

Product Life Status : **End of commercialisation**