

# Product data sheet

## Characteristics

# 8539SCA11V03A

## COMBO STARTER 600VAC 27A NEMA



by Schneider Electric

Price\*: 2150.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Contact application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Thermal magnetic circuit breaker 30 A
Enclosure type	Enclosure dust and damp proof indoor

### Complementary

Rated current	27 A
System Voltage	240 V AC 60 Hz 220 V AC 50 Hz
Control type	Pushbutton START-STOP
Depth	8.34 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	24 in
Motor power hp	5 hp 230 V AC
NEMA size	1
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker FAL
Product weight	40 lb(US)
Reset	With external
Short-circuit protection	5000 A AIR
Thermal overload type	Melting alloy
Width	9.5 in

### Environment

NEMA degree of protection	NEMA 12
Product certifications	UL listed file E152395 CCN NKJH7

### Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period

18 months

Product Life Status : **End of commercialisation**