Product data sheet
Characteristics

8539SCA41V08C
COMBO STARTER 600VAC 27A NEMA

Commercial status
This Product is Obsolete :

⚠ This Product is Obsolete

Main

Contactor application	Non-reversing
Device short name	S

Complementary

Depth	8.34 In (211.84 mm)
Device mounting	Surface
Height	24 In (609.60 mm)
Maximum Horse Power Rating	0.25…0.34 Hp 200/230 V AC 0.25…1 Hp 460/575 V AC
NEMA size	1
Number of poles	3
Number of thermal units required	3
Product destination	Circuit breaker GJL36003M01
Net Weight	40 Lb(US) (18.14 kg)
Reset	Without external
Width	9.5 In (241.30 mm)

Environment

NEMA Degree of Protection	NEMA 12
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21213-8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	45.00 Lb(US) (20.412 kg)

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.