



by Schneider Electric

Price\*: 2091.00 USD

### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Circuit breaker type	GJL36015M03
Contactor application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure standard environment indoor

### Complementary

Rated current	27 A
System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Control type	Selector switch HAND-OFF-AUTO
Depth	8.34 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	22.5 in
Motor power hp	1.5...3 hp 200/230 V AC 5...7.5 hp 460 V AC 5...10 hp 575 V AC
NEMA size	1
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker GJL36015M03
Product weight	38 lb(US)
Short-circuit protection	100000 A AIR
Thermal overload type	Melting alloy
Width	9.5 in

## Environment

NEMA degree of protection	NEMA 1
Product certifications	UL listed file E152395 CCN NKJH7

## Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	40
Returnability	N

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**