

# Product data sheet

## Characteristics

# 8539SCT3V02S

## COMBO STARTER 600VAC 27A NEMA



by Schneider Electric

Price\*: 3936.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Contact application	Non-reversing
Control circuit	Separate control circuit
Device short name	S
Disconnecter device type	Thermal magnetic circuit breaker 20 A
Enclosure type	Bolted hazardous location indoor

### Complementary

Rated current	27 A
System Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Depth	11 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Cast aluminium
Height	27.63 in
Motor power hp	10 hp 575 V AC 7.5 hp 460 V AC
NEMA size	1
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker FAL
Product weight	115 lb(US)
Short-circuit protection	5000 A AIR
Thermal overload type	Melting alloy
Width	14.25 in

### Environment

NEMA degree of protection	NEMA 7/9
---------------------------	----------

### Ordering and shipping details

Category	21217 - 8538,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	120
Returnability	N

### Offer Sustainability

RoHS (date code: YYWW)

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period

18 months

Product Life Status : **End of commercialisation**