

Product data sheet

Characteristics

8539SCW41S8V08

COMBO STARTER 600VAC 27A NEMA



by Schneider Electric

Price*: 4320.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Contact application	Non-reversing
Control circuit	Common control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure corrosion resistance indoor/outdoor

Complementary

Rated current	27 A
System Voltage	208 V AC 60 Hz
Depth	8.34 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	24.06 in
Motor power hp	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
NEMA size	1
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker GJL36003M01
Product weight	40 lb(US)
Short-circuit protection	100000 A AIR
Thermal overload type	Melting alloy
Width	9.5 in

Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	45
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**