Product data sheet
Characteristics

8539SFA52V02AS
COMBO STARTER 600VAC 135A NEMA

Commercial status
This Product is Obsolete :

⚠ This Product is Obsolete

Main

Contactor application	Non-reversing
Device short name	S

Complementary

Rated current	135 A
Control type	Push-button START-STOP
Depth	10.53 In (267.46 mm)
Device mounting	Surface
Height	52.5 In (1333.50 mm)
Maximum Horse Power Rating	30 Hp 200 V AC 60…75 Hp 460 V AC 60…100 Hp 575 V AC
NEMA size	4
Number of poles	3
Number of thermal units required	3
Product destination	Circuit breaker KAL3625025M
Net Weight	170 Lb(US) (77.11 kg)
Reset	With external
Short-circuit protection	22000 A AIR
Width	16 In (406.40 mm)

Environment

NEMA Degree of Protection	NEMA 12
Product Certifications	UL listed file E152395 CCN NKJH7

Ordering and shipping details

Category	21214-8538,39 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	175.00 Lb(US) (79.379 kg)

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.