

# Product data sheet

## Characteristics

# 8539SFW42V02AS

## COMBO STARTER 600VAC 135A NEMA



by Schneider Electric

Price\*: 13544.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Contact application	Non-reversing
Control circuit	Separate control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure corrosion resistance indoor/outdoor Enclosure dustproof indoor/outdoor

### Complementary

Rated current	135 A
System Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Control type	Pushbutton START-STOP
Depth	10.53 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	52.5 in
Motor power hp	30 hp 200 V AC 60...75 hp 460 V AC 60...100 hp 575 V AC
NEMA size	4
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker KAL3625025M
Product weight	120 lb(US)
Short-circuit protection	22000 A AIR
Thermal overload type	Melting alloy
Width	16 in

### Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E152395 CCN NKJH7

### Ordering and shipping details

Category	21218 - 8538,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	125
Returnability	N

### Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
REACH	Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**