Product data sheet
Characteristics

8606SEK1HV86S
AUTOTRFMR STARTER 600VAC 90A

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Device short name	S
Product Specific Application	OEM applications

Complementary

[Ue] rated operational voltage	600 V AC
[Uc] control circuit voltage	120 V AC
Maximum Horse Power Rating	40 Hp
NEMA size	3
Number of poles	3
Number of thermal units required	3

Environment

Product Certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21232 - 8606 S*K OEM KITS
Discount Schedule	CP1
Returnability	No
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	250.00 Lb(US) (113.398 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Not compliant

Product Life Status : End of commerc. announced

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.