

Product data sheet

Characteristics

8606SFW1LV06

AUTOTRFRMR STARTER 600VAC 135AMP



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 37084.00 USD

Main

Device short name	S
-------------------	---

Complementary

Rated current	135 A
[Ue] rated operational voltage	480 V AC
[Uc] control circuit voltage	480 V AC
Depth	406.40 Mm (16 in)
Device mounting	Surface
Height	1905.00 Mm (75 in)
Maximum Horse Power Rating	75 Hp
NEMA size	4
Number of poles	3
Number of thermal units required	3
Net weight	254.01 Kg (560 lb(US))
Width	812.80 Mm (32 in)

Environment

NEMA degree of protection	NEMA 4
Product certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21231 - 8606 (NOT S*K)
Discount Schedule	CP1
Package weight(Lbs)	249.48 Kg (550 lb(US))
Returnability	No
Country of origin	MX

Offer Sustainability

EU RoHS Directive	Not compliant
-------------------	---------------

Product Life Status : **Commercialised**