

Product data sheet

Characteristics

8606SGW1LV08

AUTOTRFMR STARTER 600VAC 270AMP



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 53734.00 USD

Main

Control circuit	Common control circuit
Device short name	S
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor

Complementary

Rated current	270 A
System Voltage	208 V AC
[Uc] control circuit voltage	208 V AC
Depth	16 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	75 in
Motor power hp	75 hp
NEMA size	5
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product weight	635 lb(US)
Thermal overload type	Melting alloy
Width	32 in

Environment

NEMA degree of protection	NEMA 4
Product certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21231 - 8606 (NOT S*K)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	575
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
------------------------	-----------------------

Product Life Status : **Commercialised**