

Product data sheet

Characteristics

8606SGW1LV08

AUTOTRFRMR STARTER 600VAC 270AMP



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 53734.00 USD

Main

Device short name	S
-------------------	---

Complementary

Rated current	270 A
[Ue] rated operational voltage	208 V AC
[Uc] control circuit voltage	208 V AC
Maximum Depth	16 In (406.40 mm)
Device mounting	Surface
Maximum Height	75 In (1905.00 mm)
Maximum Horse Power Rating	75 Hp
NEMA size	5
Number of poles	3
Number of thermal units required	3
Net Weight	635 Lb(US) (288.03 kg)
Maximum Width	32 In (812.80 mm)

Environment

NEMA degree of protection	NEMA 4
Product certifications	UL listed file E70074 CCN NLDX

Ordering and shipping details

Category	21231 - 8606 (NOT S*K)
Discount Schedule	CP1
Package weight(Lbs)	575 Lb(US) (260.82 kg)
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive-harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Not compliant

Product Life Status : **Commercialised**