

# Product data sheet

## Characteristics

# 8739SBW51V02S

## REVERSING COMBO STARTER 600VAC 18ANEM



by Schneider Electric

Price\*: 4932.00 USD

### Commercial status

This Product is Obsolete :

This Product is Obsolete

### Main

Control circuit	Separate control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure water resistant Enclosure dustproof Enclosure corrosion resistance

### Complementary

System Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Depth	11.4 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Glass polyester
Height	27 in
Motor power hp	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
Motor starter type	Reversing
NEMA size	0
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Product destination	Circuit breaker GJL36003M01
Thermal overload type	Melting alloy
Width	25.25 in

### Environment

NEMA degree of protection	NEMA 4X
Product certifications	NEMA UL listed

### Ordering and shipping details

Category	21297 - 8738,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	57
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**