

Product data sheet

Characteristics

8739SCA51V83SY74

REVERSING COMBO STARTER 600VAC 27ANEM



by Schneider Electric

Price*: 3402.00 USD

Commercial status

This Product is Obsolete :

This Product is Obsolete

Main

Control circuit	Separate control circuit
Device short name	S
Disconnecter device type	Mag-Gard circuit breaker
Enclosure type	Enclosure dust and damp proof indoor

Complementary

Rated current	27 A
Depth	10.09 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Height	24.75 in
Motor power hp	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
Motor starter type	Reversing
NEMA size	1
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	3
Permissible voltage	<= 600 V AC
Primary voltage	480 V AC 60 Hz
Product destination	Circuit breaker GJL36003M01
Product weight	52 lb(US)
Reset	With external
Secondary voltage	24 V AC 60 Hz
Thermal overload type	Melting alloy
Width	13.75 in

Environment

NEMA degree of protection	NEMA 12
Product certifications	NEMA UL listed

Ordering and shipping details

Category	21292 - 8738,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	60
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)

Will be compliant on 3Q2014

REACH

Reference not containing SVHC above the threshold

Contractual warranty

Warranty period

18 months

Product Life Status : **End of commercialisation**