

Product data sheet

Characteristics

8903LG604V02

8903L electrically held lighting contactor, 10 P, 6 NO, 4 NC, 30 A, 600 V, 110/1



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1374.00 USD



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 170 VA 50 Hz
Hold-in power consumption in VA	35 VA 60 Hz 35 VA 50 Hz
[In] rated current	20 A tungsten 30 A fluorescent
Poles description	10P 6 NO + 4 NC
Control type	No control units
Local signalling	No indicator
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.8 in (198 mm)

Environment

NEMA degree of protection	NEMA 1 painted sheet steel and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	10.800000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1431 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**