

Product data sheet

Characteristics

8903LO60V02Y145

8903L electrically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 110/120 V 50



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 903.50 USD



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz 140 VA 50 Hz
Hold-in power consumption in VA	30 VA 60 Hz 30 VA 50 Hz
[In] rated current	20 A tungsten 30 A fluorescent
Poles description	6P 6 NO
Control type	No control units
Local signalling	No indicator
Additional included device	Transient voltage suppression
Electrical connection	Screw-clamp terminals
Height	5 in (127 mm)
Depth	3.11 in (79 mm)
Width	4.25 in (108 mm)

Environment

NEMA degree of protection	Not rated (open device)
Product certifications	CSA UL listed

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	3.2600000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1431 - Schneider Electric declaration of conformity Schneider-Electric declaration of conformity
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**