

# Product data sheet

## Characteristics

# 8903PBQ10V38X22

panelboard lighting contactor, 100 AMP, 2 pole,  
panel mount, 120/208V 60Hz coil

### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Product or component type	Mechanically Held Lighting Contactor
Device short name	PB
Control circuit	Common control circuit

### Complementary

[Uc] control circuit voltage	120 V AC at 60 Hz
[In] rated current	100 A
Poles description	2P
AWG gauge	AWG 1/0 (aluminium/copper) , power wire AWG 18...AWG 10 (copper) , control wire
System Voltage	600 V AC
Auxiliary contact composition	2 NO + 2 NC
Mounting support	Panel
Electrical connection	Lugs
Height	11.73 in (298 mm)
Depth	3.86 in (98 mm)
Width	7.52 in (191 mm)

### Environment

Product certifications	CSA UL listed
------------------------	------------------

### Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	MX

Product Life Status : **End of commercialisation**