

Product data sheet

Characteristics

8903PBR11V38X22

panelboard lighting cont, 150 AMP, 3 pole, panel mount, 120/208V 60Hz coil

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Product or component type	Mechanically Held Lighting Contactor
Device short name	PB
Control circuit	Common control circuit

Complementary

[Uc] control circuit voltage	120 V AC at 60 Hz
[In] rated current	150 A
Poles description	3P
AWG gauge	AWG 18...AWG 10 (copper) , control wire 350 kcmil (aluminium/copper) , power wire
System Voltage	600 V AC
Auxiliary contact composition	2 NO + 2 NC
Mounting support	Panel
Electrical connection	Lugs
Height	14.49 in (368 mm)
Depth	3.86 in (98 mm)
Width	7.52 in (191 mm)

Environment

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	MX

Product Life Status : **End of commercialisation**