

Product data sheet

Characteristics

8903PBW11BV28R

panelboard lighting cont, 225 AMP, 3 pole, bus mount, 480V 60Hz coil, repair

Commercial status

This Product is Obsolete :

 This Product is Obsolete

Main

Product or component type	Mechanically Held Lighting Contactor
Device short name	PB
Control circuit	Common control circuit

Complementary

[Uc] control circuit voltage	480 V AC at 60 Hz
[In] rated current	225 A
Poles description	3P
AWG gauge	AWG 18...AWG 10 (copper) , control wire 350 kcmil (aluminium/copper) , power wire
System Voltage	600 V AC
Auxiliary contact composition	Without
Mounting support	Busbar
Electrical connection	Busbar connection
Height	9.49 in (241 mm)
Depth	3.39 in (86 mm)
Width	7.52 in (191 mm)

Environment

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21323 - 8903 PB
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	Y
Country of origin	US

Product Life Status : **End of commercialisation**