Product data sheet
Characteristics

8903PBW11V28R
panelboard lighting cont, 225 AMP, 3 pole, panel mount, 480V 60Hz coil, repair

Commercial status
This Product is Obsolete :

⚠ This Product is Obsolete

Main

Product or Component Type	Mechanically Held Lighting Contactor
Device short name	PB
Control circuit	Common control circuit

Complementary

[Uc] control circuit voltage	480 V AC 60 Hz
Line Rated Current	225 A
Poles description	3P
AWG gauge	350 kcmil aluminium/copper)power AWG 18...AWG 10 copper)control
[Ue] rated operational voltage	600 V AC
Auxiliary contact composition	Without
Mounting support	Panel
Electrical Connection	Lugs
Height	14.49 In (368 mm)
Depth	3.86 In (98 mm)
Width	7.52 In (191 mm)

Environment

Product Certifications	UL Listed[RETURN]CSA

Ordering and shipping details

Category	21323-8903 PB
Discount Schedule	CP1
Returnability	No
Country of origin	US

Contractual warranty

Warranty	18 months

Product Life Status : End of commerc. - Block

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein.
This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.
It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof.
Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.