

Product data sheet

Characteristics

8903SQH3V04

lighting contactor, electrically held, 100 A, 4 pole,
NEMA 3R, 277V 60Hz



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2484.00 USD



Main

Product or component type	Electrically Held Lighting Contactor
Range of product	S
Control circuit	Separate control circuit

Complementary

[Uc] control circuit voltage	277 V AC 60 Hz
Line Rated Current	100 A
Poles description	3P
Control type	No control units
Local signalling	No indicator
Auxiliary contact composition	Without
Additional included device	None
Electrical connection	Lugs
Height	643 mm
Depth	8.62 in (219 mm)
Width	12.83 in (326 mm)

Environment

NEMA degree of protection	NEMA 3R painted sheet steel surface and none
Product certifications	CSA UL listed

Ordering and shipping details

Category	21325 - 8903 S (NOT S*C) ELECT.
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	9.75
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014
------------------------	-----------------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status :	Commercialised
-----------------------	-----------------------