

# Product data sheet

## Characteristics

# 8940PF2V06

## PUMP PANEL 480VAC 135AMP NEMA +OPTIONS

Price\*: 23400.00 USD

### Commercial status

This Product is Obsolete :

 This Product is Obsolete

### Main

Control circuit	Common control circuit
Disconnecter device type	Associated circuit breaker
Enclosure type	Enclosure weatherproof indoor/outdoor
Range of product	Well-Guard

### Complementary

System Voltage	480 V AC 60 Hz 440 V AC 50 Hz
Control type	Selector switch HAND-OFF-AUTO Push-button START
Depth	13.25 in
Device mounting	Surface
Electrical connection	Screw terminal
Height	47 in
Motor power hp	100 hp 480 V AC
NEMA size	4PW
Network number of phases	3 phases
Number of poles	3
Number of thermal units required	6
Permissible voltage	<= 480 V AC
Thermal overload type	Ambient compensated bimetallic
Width	30 in

### Environment

NEMA degree of protection	NEMA 3R
Product certifications	NEMA UL listed

### Ordering and shipping details

Category	21394 - 8940 M,P,R,V
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	Y

### Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **End of commercialisation**