

Product data sheet

Characteristics

8940WC3S2V81FF4H30P51P52TX20

Well-Guard Pump Panel Size 1, Motor Logic SSOLR, 480 VAC, NEMA 3R +Options

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range	Square D
Product name	Well-Guard Control
Device short name	S2
Device application	Pumping

Complementary

Control circuit	Control circuit transformer
[Uc] control circuit voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Line Rated Current	27 A
Number of poles	3
Motor power hp	10 hp at 480 V AC for 3 phases
Permissible voltage	600 V at AC
Control type	(HAND-OFF-AUTO) selector switch
Disconnecter device type	Fusible disconnect switch
Associated fuse rating	30 A
Fuse type	H or K
Thermal overload type	Motor Logic solid state class 10/20
Protection type	Overload Phase unbalance Phase loss
Device mounting	Surface
Electrical connection	Screw terminal
NEMA size	1
Height	38.5 in (978 mm)
Width	20.43 in (519 mm)
Depth	9.41 in (239 mm)

Environment

NEMA degree of protection	NEMA 3R
Enclosure type	Weatherproof enclosure indoor/outdoor
Product certifications	NEMA UL listed

Ordering and shipping details

Category	21393 - 8940 WC,WD
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	94
Returnability	N
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Product Life Status : **Commercialised**