



by Schneider Electric

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 208.00 USD



### Main

Range of product	Harmony 9001K
Product or component type	Illuminated push-button
Device short name	K
Type of operator	Spring return
Operator profile	Green flush
Operator additional information	Full guard in plastic

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	1.18 In (30 mm)
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Via integral transformer
[Us] rated supply voltage	110...120 V AC
Contacts type and composition	1 NO
Connections - terminals	Screw clamp terminals
Operating position	Any position
[Ie] rated operational current	10 A, AC-15 10 A, DC-13
Contact operation	Standard
Device presentation	Complete product

### Environment

Product certifications	NEMA CE UL listed file E42259 CCN NKCR CSA LR 25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

## Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901026969
Package weight(Lbs)	0.57 Lb(US) (0.26 kg)
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**