



by Schneider Electric



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

| | |
|---------------------------------|----------------------------------|
| Range of product | Harmony 9001K |
| Product or component type | Complete illuminated push-button |
| Device short name | 9001K |
| Bezel material | Chromium plated metal |
| Mounting diameter | 30 Mm |
| Operator additional information | Full guard in plastic |
| Light source | Incandescent |

Complementary

| | |
|------------------------------|---|
| Shape of signaling unit head | Round |
| Type of operator | Spring return |
| Operator profile | Flush, unmarked |
| Bulb base | BA 9s |
| Light block supply | Via integral transformer 220...240 V AC 25/30 Hz 6 V) |
| Mechanical durability | 5000000 Cycles |
| Operating position | Any position |
| Net weight | 0.166 Kg |

Environment

| | |
|---------------------------------------|--|
| Standards | EN/IEC 60947-5-1 CSA C22.2 No 14 JIS C 852 EN/IEC 60947-1 EN/IEC 60947-5-4 UL 508 JIS C 4520 |
| Product certifications | NEMA UL 508 |
| Protective treatment | TC |
| Ambient air temperature for storage | -40...70 °C |
| Ambient air temperature for operation | -25...70 °C |
| Vibration resistance | 7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6 |
| Shock resistance | 50 gn conforming to IEC 60068-2-27 |
| Electrical shock protection class | Class II conforming to IEC 61140 |

| | |
|---------------------------|---|
| IP degree of protection | IP66 conforming to IEC 60529 |
| NEMA degree of protection | NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4 |

Product Life Status : **End of commercialisation**