



Commercial status

End of Commercialisation :

⚠ End of Commercialisation

Main

Range of product	Harmony 9001K
Product or component type	Complete illuminated push-button
Device short name	9001K
Bezel material	Chromium plated metal
Mounting diameter	30 Mm
Operator additional information	Screw-on plastic mushroom
Light source	Yellow LED

Complementary

Shape of signaling unit head	Round
Type of operator	Spring return
Operator profile	Yellow mushroom Ø 35 mm, unmarked
Bulb base	BA 9s
Light block supply	Direct 12...14 V AC/DC
Mechanical durability	5000000 Cycles
Operating position	Any position
Net weight	0.166 Kg

Environment

Standards	EN/IEC 60947-5-4 EN/IEC 60947-5-1 JIS C 4520 UL 508 JIS C 852 EN/IEC 60947-1 CSA C22.2 No 14
Product certifications	NEMA UL 508
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...70 °C
Vibration resistance	7 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	50 gn conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to IEC 61140

IP degree of protection	IP66 conforming to IEC 60529
NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3R NEMA 4

Product Life Status : **End of commercialisation**